# Polywipe-C SecureGuard Wiper

Standardweight 100% polyester interlock knit wiper

## **Description**

The Polywipe-C SecureGuard Wiper is standardweight with a textured surface for effective cleaning. The wiper is laser-cut, which seals the fibers at the edges. The wiper is made with fabric knitted from filament polyester and packaged in a cleanroom to further reduce contamination. Contec's PCSG products are specially processed to provide a high quality wiper at a very competitive costs

#### **Features and Benefits**

- Soft textured wiper cleans surfaces without scratching
- Good sorbency with solvents
- Compared low in both particle and fiber
- Chemical resistant
- Economical

## **Applicability**

The information presented here is applicable to the part numbers shown below as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.

### **Technical Data**

Attribute; (units)	Value**	Test Method
Basis weight; (g/m²)	107	
Sorbency in water Intrinsic; (mL/g) Extrinsic; (mL/m²)	2.60 292	IEST-RP-CC004.3, Sec. 8.1
Sorptive rate; (seconds)	< 1	IEST-RP-CC004.3, Sec. 8.2
Non-volatile residue, NVR In deionized water; (g/m²) In isopropanol; (g/m²)	0.03 0.03	IEST-RP-CC004.3, Sec. 7.1.2
Particles, readily releasable $P\!\geqslant\!0.3\mu\text{ m; }(x10^6/m^2)$ $P\!\geqslant\!0.5\mu\text{ m; }(x10^6/m^2)$	N/A 16.5	IEST-RP-CC004.2, Sec. 5.1
Fibers > $100 \mu$ m; $(x10^3/m^2)$	0.80	IEST-RP-CC004.2, sec. 5.2

Part #	Description	Packaging
PCSG-99	9" x 9" (23 x 23cm) wiper	150 wipers/bag, 12 bags/case
PCSG-99B	9" x 9" (23 x 23cm) wiper, bulk packaged	300 wipers/bag, 5 bags/case
PCSG-1212	12" x 12" (30.5 x 30.5cm) wiper	75 wipers/bag, 10 bags/case
PCSG-1212B	12" x 12" (30.5 x 30.5cm) wiper, bulk packaged	150 wipers/bag, 6 bags/case

#### Notes:

- 1) Data shown are typical values and should not be used as product specifications.
- 2) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 3) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 07/06/2011



www.contecinc.com